

KERN HFD 1T-4

Robust, high-resolution crane scale

KERN



Category

Brand	KERN
Product category	Industrial scale
Product group	Crane scale
Product family	HFD

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	300 kg; 600 kg; 1500 kg
Readability [d]	0,1 kg; 0,2 kg; 0,5 kg
Reproducibility	0,1 kg; 0,2 kg; 0,5 kg
Linearity	± 0,2 kg; 0,4 kg; 1 kg
Resolution	3.000, 3.000, 3.000
Tare range	1499,5 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	1500 kg (M1)
Stabilization time	2 s
Warm-up time	10 min; 10 min; 10 min
Load cell connection	4-wire
Eccentric/Off-centre loading is not possible	✓
Construction type of the scale	Multi-range balance
Units	kg
Internal measuring frequency	10 Hz
Tolerance (% of [Max])	0,2%
Maximum creep (15 minutes)	2 kg
Maximum creep (30 minutes)	4 kg
Default unit	kg
Loadcell type	HS-16 3T

Display

Display type	LCD
Display backlight	LED white
Display screen size	115×40 mm
Display digit height	30 mm
Languages of the user interface	Symbol language

Construction

Dimensions completely mounted (W×D×H)	422×194×129 mm
Dimension display device (W×D×H)	194×160×129 mm
Dimensions housing - width (A)	194 mm
Dimensions housing - depth (B)	129 mm
Dimensions housing - height/length (C)	160 mm
Dimensions - total height/total length (D)	422 mm
Dimensions - inner length (E)	384 mm
Dimensions loop/top - hole diameter (F)	50,8 mm
Dimensions hook/bottom - hole diameter (G)	50,8 mm
Dimensions loop/top - thickness (H)	19 mm
Dimensions hook/bottom - thickness (I)	19 mm
Material housing	cast aluminium
Material suspension	unalloyed forged steel
Material load hook	unalloyed forged steel
Material load cell(s)	high-alloy steel
Load cells - number	1

Functions

Sum memory function	✓
Recipe/summing level	Sum A
Wireless operation	✓
Capacity - Display	✓
Range of radio module	20 m
Standby function	✓
Hold function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off 5 min 15 min
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (single & multi)
Number of keys for operation	5

KERN HFD 1T-4

Robust, high-resolution crane scale

KERN

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Input voltage power supply / power [Max]	110 V - 240 V AC
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 2500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	Li-Ion
Battery	1×12 V, Type 23 A
Battery connection	Plug-in terminals
Battery capacity	5.200 mAh
Battery voltage	7,4 V
Battery - Number of cells	8
Battery - Individual weight	193 g
Battery - Total weight	1544 g
Battery capacity (Wh)	38,48 Wh
Battery - Lithium content	36,6 mg
Battery - Tests passed UN 38.3	✓
Rechargeable battery	7,4 V, 5200 mAh
Rechargeable battery operating time - backlight on	30 h
Rechargeable battery operating time - backlight off	70 h
Rechargeable battery charging time	12 h
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	0 %
Humidity of environment [Max]	80 %

Approval

CE mark	✓
TÜV-tested	✓

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for DAkkS calibration	963-130H
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	740×270×280 mm
Shipping method	Parcel service
Net weight approx.	9 kg
Gross weight approx.	10 kg
Shipping weight	11,2 kg

Product information

GTIN/EAN number	4045761202757
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

