

K3

Infrared Thermometer Forehead

Advantages

1S

Quick Measurement

±0.2

High Accuracy



Alarm Function

1W

One Week Standby



°C/°F Unit Available



Energy Saving



Technical Data

Accuracy	±0.2 degrees	Response time	0.5s
Abnormal automatic alarm	flashing +“Di Di” sound	Charging method	USB charging or battery.
Automatic measurement	measuring distance 5cm ~ 10cm	Input	USB DC 4.2-5V
Standby	About one week	Weight	350g
Install method	nail hook, double-sided adhesive sticking, bracket fixing	Dimensions	170*115*140mm
Operating temperature	10℃~40℃ (Recommend 15℃~35℃)	Infrared measuring range	0~50℃
Standby	5s (Red dot dynamic cycle)	Screen	Digital display

Quick measurement

Accurate feedback

Fever alarm

© Accurate temperature measurement

CE FC RoHS
Made in China

