



## LC-M29-UW-UXGA-100-C - 29" ultra-wide curved monitor -

Experience the ultimate gaming feeling with the **29" / 73,66 cm** monitor from LC-Power!

Due to the **UW-UXGA** resolution of 2560 x 1080 pixels the monitor delivers razor-sharp pictures.

Immerse yourself in a fascinating gaming & entertainment world with a **1200R** curvature and a **21:9 ultra-wide widescreen format**.

Advanced **VA panel technology** minimizes light scatter across the entire screen and gives you deep blacks thanks to a contrast ratio of **3000:1**.

Other features of the monitor include a screen refresh rate of **100 Hz** for a fluent display of content, **FreeSync** for a smooth gameplay as well as an **in height adjustable stand**.

**See sharper thanks to LC-Power!**

### Technical specification - LC-M29-UW-UXGA-100-C

Display size:	29" / 73,66 cm
Resolution:	UW-UXGA / 2560 x 1080 pixels
Screen refresh rate:	100 Hz
Panel type:	VA (Samsung)
Aspect ratio:	21:9
Brightness:	250 (± 30) cd/m <sup>2</sup>
Contrast ratio:	3000:1
Display colours:	16,7 millions
Viewing angle:	H: 178° / V: 178°
Curvature:	1200R
Response time:	OD 6 ms
Interface:	2x HDMI 1.4 / 1x DP 1.2
Audio:	1x Audio out (3,5 mm jack)

Included in delivery: monitor, base, DP cable, power cord, mounting material, user manual

Features:	FreeSync, Overdrive, Low Blue, Flicker-Free, VESA compatible, height adjustable stand
Colours:	back side: black base: black
Dimension (without base):	694 x 319 x 116 mm
Dimension (with base):	694 x 411 x 187 mm
Dimension (retail):	791 x 387 x 165 mm
Base tilt:	-5°~15°
VESA mounting:	75 x 75 mm
Weight (product/overall):	4,5 / 6,8kg
Consumption:	36 W (typ.)
Standby:	≤ 0,5 W
Power input:	AC 100-240V 50/60Hz 12V/4A
Mark of conformity:	CE
Barcode:	4260070127755
Manufacturer code:	LC-M29-UW-UXGA-100-C