


**NOTE:**

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 10MΩ;
  - Contact resistance:5Ω Max;
- PRINT WORD:USB CABLE AWM 80°C 30V VW-1 28AWG  
×1P 28AWG×2C LS-19
- PACKING:1PCS/GIFT BOX
- RoHS3.0 AND REACH COMPLIANT



**MATERIAL LIST:**

NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
④	OUTER MOLD	PVC COLOR FOR TRANSPARENT	2	
③	USB B TYPE	USB B/M, WHITE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
②	USB A TYPE	USB A/M, WHITE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
①	CABLE	USB2.0 28AWG BC*1P+28AWG*2C+AL-FOIL+BRAID AL-MG PVC/TRANSPARENT JACKET OD:4.2±0.2MM	1	

ITEM NO.	Model no.	LENGTH	Packing
2269072	712123T, 81	1800+100/-0	VP1-1:105 x 140(depth:20mm)
2269074	712123T, 03	3000+100/-0	VP1-2:105 x 140(depth:30mm)
2269073	712123T, 05	5000+100/-0	VP1-2:105 x 140(depth:30mm)

NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
		NEW	2021.03.19	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

RENKFORCE					
CUSTOMER	RENKFORCE			ITEM NO.	SEE THE CHART
PRODUCT NAME	USB 2.0 AM/BM Cable			UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
FERGUS	ALVAN		2021.03.19		