



P1



PIN OUT



P2

NOTE:

1. Electrical test:
  - (1) 100% open short & miss wire test
  - (2) HDTV-DVD TEST, 3840\*2160@60Hz PASS.
2. Operation temperature: 0°C ~ +45°C  
 Storage temperature: -20°C ~ +70°C  
 Operation humidity: 10% ~ 85%  
 Storage humidity: 10% ~ 85%
3. RoHS 2.0 and REACH COMPLIANT
4. PACKING: 1 PCS/Renkforce giftbox

P1	P2	P1	P2
1	1	13	13
3	3	14	14
2	2	15	15
4	4	16	16
6	6	17	17
5	5	18	18
7	7	19	19
9	9		
8	8	SHELL	SHELL
10	10		
12	12		
11	11		

MATERIAL LIST:

⑤	THUMB SCREW	#4-40*15 PLATED NICKEL	1	
④	SCREW NUT	NUT-NICKEL PLATED #4-40	1	
③	MOLDED	45P BLACK PVC	1	
②	MOLDED	LDPE	1	
①	CONNECTOR	P1&P2:HDMI 19PIN FEMALE+PCB:SOLDER TYPE, GOLD FLASH CONTACTS, Nickel PLATED SHELL BLACK INSULATION	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
		NEW	2018-07-23	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER	CN	ITEM NO.			
PRODUCT NAME	HDMI 19P AF TO AF WITH FLANGE	UNO ITEM NO.	762111	UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
Alvan	Alvan		2018-07-23		

