



### TECHNICAL INFORMATION

Watts:	18
Input Power:	AC:100-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	Black
Body Type:	ABS Plastic
Operation Temperature:	-35°C to +55°C
Dimmable:	No
Dimension:	73x27x43mm
Output Voltage:	DC:12V
Output Current:	1.5A

### PLASTIC POWER SUPPLY

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 3237 - 1407 938

[View more details](#)



### FEATURES

- Rainproof drivers are compatible with all V-TAC Strip lights, LEDs etc.
- Short circuit protection, overload protection and stable output voltage
- Built-in EMI Filter
- High efficiency and low temperature
- 100% load tested
- IP44 Ingress protection
- CE, ROHS and EMC approved

CE/EMC

CE/LVD



### PACKAGING

Gross Weight (Kgs): 0.111  
Unit CBM: 0.00026775  
Dimension: 73x27x43mm

### MASTER BOX PACKAGING

Box Qty: 120  
Qty Per Pallet: 3000  
Length (Box) mm: 95  
Width (Box) mm: 85  
Height (Box) mm: 32

### LISTING DETAILS

Commodity Code: 8504409090  
Ean Code: 3800157628037