



TECHNICAL INFORMATION

Input Power:	DC:12V
Long Life:	20,000 Hours
LED Chip Type:	SMD
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	120°
Color:	RGB
Dimension:	10mm
Watts per meter:	4.8
Lumens per meter:	500
Current per meter:	0.4A
No. Of Led:	30
Roll Qty:	5M

STRIPLIGHTS 5050 30 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 2124 -

[View more details](#)



FEATURES

- Stable SMD technology for better reliability and longer lifespan
- Low Voltage flexible ribbon available in DC:12V
- 5M Roll quantity
- Flexible installation: Cutting and reconnect the strip as you wish to suit your application
- Suitable for illuminating borders, edges, cabinets, bars and areas with limited space for installation

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 0.023
Unit CBM: 0.0000735
Dimension: 10mm

MASTER BOX PACKAGING

Box Qty: 400
Qty Per Pallet: 9600
Length (Box) mm: 10
Width (Box) mm: 210
Height (Box) mm: 260

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800230621535