

TEMPO TPC 241911T



Order symbol: TPC 241911T
Product nbr: 5824007
Description: Enclosure, PC
Remarks: Clear transparent cover

EAN: 6418074086778
EI. number:
Finland:

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	240	191	107	DR 210 DIN-35 Mounting rail
inch:	9.4	7.5	4.2	EKV 12 DIN-35 Mounting rail
				FP 10674

Materials:	Material:	Rating:
Material:	Polycarbonate	Ingress Protection (EN 60529): IP65
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK07/IK08
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey	Flammability Rating: UL 746C 5"
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 4, 4X, 12

Temperatures:	Certificates:
Temperature °C (short term):	SGS Fimko
Temperature °C (continuous):	
Temperature °F (short term):	
Temperature °F (continuous):	

Accessories:
MP 2419 Mounting plate

