



Public information	Result
Energy efficiency class for Standard Dynamic Range (SDR)	G
On mode power demand for Standard Dynamic Range (SDR) (W)	103
Energy efficiency class in High Dynamic Range (HDR) mode	n.a.
On mode power demand in High Dynamic Range (HDR) mode (W)	n.a.
Off mode, power demand (W)	0.3
Standby mode power demand (W)	1.5
Networked standby mode power demand (W)	3
Electronic display category	Monitor
Size ratio (X : Y)	16:9
Screen resolution (Horizontal x Vertical) (pixels)	3840x2160
Screen diagonal (cm / inches)	138.8/55
Visible screen area (cm ²)	8230
Panel technology used	LED LCD
Automatic Brightness Control (ABC) available	Yes
Voice recognition sensor available	No
Room presence sensor available	No
Image refresh frequency rate (Hz)	60
Power supply type	Internal
EXTERNAL STANDARDISED POWER SUPPLY (INCLUDED IN THE PRODUCT BOX)	
Standard name	n/a
Input voltage (V)	100-240Vac
Output voltage (V)	n/a
EXTERNAL STANDARDISED SUITABLE POWER SUPPLY (IF NOT INCLUDED IN THE PRODUCT BOX)	
Standard name	n.a.
Required output voltage (V)	n.a.
Required delivered current (A)	n.a.
Required current frequency (Hz)	n.a.
Minimum guaranteed availability of software and firmware updates (until)	
Minimum guaranteed availability of spare parts (until)	
Minimum guaranteed product support (until)	