

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013

| INFORMATION                                                                   |                | Value              | Unit            |
|-------------------------------------------------------------------------------|----------------|--------------------|-----------------|
| 1. Supplier name or trademark                                                 |                | HP, Inc.           |                 |
| 2. Model identifier                                                           |                | HP V24i HSD-0066-V |                 |
| 3. Energy Efficiency Class for standard Dynamic Range (SDR)                   |                | D                  |                 |
| 4. On mode power demand for Standard Dynamic Range (SDR)                      |                | 13.2               | W               |
| 5. Energy Efficiency Class for standard Dynamic Range (HDR)                   |                |                    |                 |
| 6. On mode power demand in High Dynamic Range (HDR) mode                      |                |                    | W               |
| 7. Off mode, power demand                                                     |                | 0.1                | W               |
| 8. Standby mode power demand                                                  |                | 0.2                | W               |
| 9. Networked standby mode power demand                                        |                |                    | W               |
| 10. Electronic display category                                               |                | Monitor            |                 |
| 11. Size ratio                                                                |                | 16 : 9             |                 |
| 12. Screen resolution (pixels)                                                |                | 1920 x 1080        | pixels          |
| 13. Screen diagonal                                                           |                | 60.5               | cm              |
| 14. Screen diagonal                                                           |                | 24                 | inches          |
| 15. Visible screen area                                                       |                | 1562.5             | cm <sup>2</sup> |
| 16. Panel technology used                                                     |                | LED LCD            |                 |
| 17. Automatic Brightness Control (ABC) available                              |                | No                 |                 |
| 18. Voice recognition sensor available                                        |                | No                 |                 |
| 19. Room presence sensor available                                            |                | No                 |                 |
| 20. Image refresh frequency rate                                              |                | 60                 | Hz              |
| 21. Minimum guaranteed availability of software and firmware updates (until): |                | 30 09 2029         |                 |
| 22. Minimum guaranteed availability of spare parts (until)                    |                | 30 09 2028         |                 |
| 23. Minimum guaranteed product support (until)                                |                | 30 09 2028         |                 |
| 24. Power supply type:                                                        |                | Internal           |                 |
| i External standardised power supply (included in the product box)            | Standard name  |                    |                 |
|                                                                               | Input voltage  |                    | V               |
|                                                                               | Output voltage |                    | V               |
| ii External standardised suitable power                                       |                | Standard name      |                 |

| INFORMATION                                 |                            | Value | Unit |
|---------------------------------------------|----------------------------|-------|------|
| supply (if not included in the product box) |                            |       |      |
|                                             | Required output voltage    |       | V    |
|                                             | Required delivered current |       | A    |
|                                             | Required current frequency |       | Hz   |