

## Data Sheet

# MECHANICAL BUZZER

### Technical data

#### Specifications:

Standard operating voltage	4.5VDC
Max Operating voltage	10VDC
Impedance	2200Ω
Sensitivity	-40dB ±3dB
Signal to noise ration	55dB
Operating temperature	-20°C to +60°C
Storage Temperature	-30°C to +70°C
Frequency	100 Hz to 10,000 Hz
Max Current Consumption	0.5mA
Directivity	Omni-directional

### Frequency response

