

## Data Sheet

---

### Shrinking tube set 2:1 170pcs/set



Section	Heat shrink tube		Length	Color	pcs
	Inner diameter $\varnothing$	after shrink $\varnothing$			
1	1.0 mm	$\leq 0.65$ mm	100 mm	Black	60
2	2.0 mm	$\leq 1.00$ mm	100 mm	Black	40
3	3.0 mm	$\leq 1.50$ mm	100 mm	Black	30
4	4.5 mm	$\leq 2.30$ mm	100 mm	Black	20
5	6.0 mm	$\leq 3.00$ mm	100 mm	Black	10
6	9.0 mm	$\leq 4.50$ mm	100 mm	Black	10

### Technical data

Material: Polyethylene(PE)

Shrinking ratio: 2:1

Operating Temperature:  $-55^{\circ}\text{C} \sim 110^{\circ}\text{C}$

Minimum shrink temperature:  $70^{\circ}\text{C}$

Full recovery temperature:  $110^{\circ}\text{C}$