



Sockets:

8×DIN 49440 45° degree Compliant VDE0620-1
16A/4000W, AC250V, IP20
CE certified

Cable:

2,0m H05VV-F 3G 1,5mm² with German
type earth contact plug CEE7
Cable:VDE certified
Plug: VDE certified

Profile:

IHE, Aluminum alloy black RAL9004

Plastic material:

Fireproof Polypropylene Color:black RAL9004

Holding flanges :

SPCC Thickness 2.0mm * 2

Switch:

2-poles, illuminated , red
VDE certified

Certificate for the Whole PDU:

Have GS certificate,Have CE certificate

Packing:

1pcs/PE bag + Inner carton

NOTE:

- 1:TESTING:100% OPEN SHORT
- 2.ROHS 2.0 & REACH COMPLIANT
- 3.Storage Temperature:-25~+65°C
Operation Temperature:-5~+45°C
Storage humidity:(5-90%)RH
Operation humidity:(5-90%)RH
- 4.Accessory:Standard Screw Nut Set

(Set=screw(PHILLIPS/SLOT) M6*12+Washer+M6 cage nut)

CUSTOMER		CN		ITEM NO.	2302124		
PRODUCT NAME	PDU CEE7/7 90° angled plug to 8 x DIN 49440 Socket+switch	UNO ITEM NO.	811481	UNIT	MM		
Arvin	Add Accessory	2021-02-03	A1	DRAWNBY	CHECKBY	APPOBY	
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	Arvin	Alvan	2020-05-26