



MUV USB (4xA)


Innovative 2-pole world travel adapter with 4 integrated USB ports

With the World Adapter MUV USB (4xA) from SKROSS® travellers from all over the world can charge four USB devices and connect one unearthed 2-pole device simultaneously. The travel adapter comes in an appealing compact shape and can be used in more than 220 destinations worldwide.


Suitable for



Compatibility (Input)



Compatible with the following socket types



Packaging (Retail)



Product Category

- World Travel Adapter: MUV series

Technical Specifications

- Designed in Switzerland
- Suitable for equipment with unearthed plugs (2-pole)
- Input plugs: Euro, Australia/China, UK (*not in the Swiss version), USA/Japan
- Output plugs: Euro, Australia/China, UK, USA/Japan
- Input voltage: 100 V – 250 V, 50/60 Hz
- Max. load: 2.5 A
- Power rating: e.g. 100 V – 250 W / 250 V – 625 W
- Replaceable fuse: T 2.5 A
- 4 x Type-A USB Output: 5.0 V DC / Max. 4.8 A (shared), Max. 24.0 W
- Average active efficiency: 86.9 %
- Efficiency at low load (10 %): 86.4 %
- No-load power consumption: 0.03 W
- Does not convert voltage

Weight

- Adapter: 157 g
- Adapter + packaging: 229 g

Dimensions

- Adapter: W 63 mm H 54 mm D 75 mm
- Adapter + packaging: W 105 mm H 111 mm D 73 mm

Packaging Unit

- Master carton retail: 20
- Dimensions master carton retail: W 375 mm H 250 mm D 220 mm
- Pallet: 1400 pcs

Standard Colour

- White

Description	Article-No.	EAN-Code	Made in Thailand
MUV USB (4xA), retail, white	1.302961	7640166323716	
MUV USB (4xA), CH version, retail, white	1.302965	7640166324089	
MUV USB (4xA), Asia version, retail, white	1.302966	7640166324096	