



MUV USB (AC)

Innovative 2-pole world travel adapter with integrated Dual USB Charger (1x USB C & 1 x USB)

With the World Adapter MUV USB (AC) from SKROSS® travellers from all over the world can charge a USB C device as well as a regular USB device while connecting one unearthed 2-pole device simultaneously. The travel adapter comes in an appealing compact shape and can be used in more than 220 destinations worldwide.


Suitable for



Compatibility (Input)



Compatible with the following socket types



Packaging (Retail)



Product Category

- World Travel Adapter: MUV series

Technical Specifications

- Designed in Switzerland
- Suitable for equipment with unearthed plugs (2-pole)
- Input plugs: Euro, Australia/China, UK (*not in the Swiss version), USA/Japan
- Output plugs: Euro, Australia/China, UK, USA/Japan
- Input voltage: 100 V – 250 V, 50/60 Hz
- Max. load: 2.5 A
- Power rating: e.g. 100 V – 250 W / 250 V – 625 W
- Replaceable fuse: T 2.5 A
- 1 x Type-C USB Output: 5.0 V DC / Max. 3.0 A, Max. 15.0 W
- 1 x Type-A USB Output: 5.0 V DC / Max. 2.4 A, Max. 12.0 W
- Average active efficiency: 86.4 %
- Efficiency at low load (10 %): 85.3 %
- No-load power consumption: 0.03 W
- Does not convert voltage

Weight

- Adapter: 157 g
- Adapter + packaging: 229 g

Dimensions

- Adapter: W 63 mm H 54 mm D 75 mm
- Adapter + packaging: W 105 mm H 111 mm D 73 mm

Packaging Unit

- Master carton retail: 20
- Dimensions master carton retail: W 375mm H 250 mm D 220 mm
- Pallet: 1400 pcs

Standard Colour

- White

Description	Article-No.	EAN-Code	Made in Thailand
MUV USB (AC), retail, white	1.302962	7640166323709	
MUV USB (AC), CH version, retail, white	1.302967	7640166324102	
MUV USB (AC), Asia version, retail, white	1.302968	7640166324119	