
Data Sheet

Indicator

Version 08/20



Specification

Mounting diameter	12 mm
LED color	RGB
LED voltage	12V
Head shape	Flat head
Body material	Stainless steel
Terminal	Wiring(24AWG, about 15cm)
Operating and storage temperature	-25 to +55 °C
Led life	40000 hours
Base material	PA
IP rating	IP67