



Mounting hole



NOTE:

1. 100% OPEN SHORT, MISS WIRE TEST
2. Impedance:50 Ω
3. VSWR≤1.1dB
4. Operation Temperature:-30~70℃
Storage temperature:-10℃~+60℃
Operation Humidity:10-90%
Storage Humidity:10-90%
5. Printing:RG-58/U 50 OHM COAXIAL CABLE
6. ROHS2.0 AND REACH COMPLIANT

MATERIAL LIST:

④	RP-SMA SOCKET, The shell Gold-plated	1pcs	
③	RP-SMA PLUG, The shell Gold-plated	1pcs	
②	Heat shrink tube	2pcs	
①	RG58/U Cable, 0.8mm BC+LDPE+Braid(BC)+Jacket PVC/BLACK, OD:5.0±0.2mm	1pcs	
NO.	SPECIFICATION STANDARD	QT'Y	REMARK

Item No.	Length(m)
29212c352a	1000±20
29212c352b	2000±30
29212c352c	5000±100
29212c352d	10000±300

NO.		SPECIFICATION STANDARD		QT'Y	REMARK
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.

DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED		CUSTOMER			
TOLERANCE	mm	CEI Conrad		ITEM NO.	see the sheet
.X	±0.2	PRODUCT NAME		WLAN antenna extension cable [1x RP-SMA plug - 1x RP-SMA socket]	UNO ITEM NO. 219020
.XX	±0.10	DRAWNBY		Arvin	CHECKBY
.XXX	±0.005	APPROVE		Alvan	DATE
PROJECTION		DATE		2020-09-21	