

Audio Extractor HDMI SPDIF + RCA R/L



Features:

- ▶ HDMI resolution: 24 / 50 / 60fs / 1080p / 1080i / 720p / 576p / 576i / 480p / 480i
- ▶ Support at video color format: 24bit deep color 30bit, 36bit
- ▶ Audio output: L/R+SPDIF
- ▶ Max bandwidth: 225MHz/6.75Gbps
- ▶ Input/Output TMDs signal: 0,5 ~ 1,5 Volts p-p(TTL)
- ▶ Input/Output DDC signal: 5 Volts p-p(TTL)
- ▶ Input cable distance: ≤15m AWG26
- ▶ Output cable distance: ≤ 20m AWG26
- ▶ Max working current: 500mA
- ▶ Power adapter: input AC(50/60Hz), 100V-240V, output DC5V/1A
- ▶ Operating temperature: -15 / +55 °C
- ▶ Operating humidity range: 5 / 90% RH (no condensation)
- ▶ Dimensions: 84.5 x 61.8 x 21 mm

Package contents:

- ▶ Audio Extractor IDATA HDMI-EA
- ▶ Power adapter 5V 1A
- ▶ Installation guide



Available colors:

black



IDATA HDMI-EA

Color: black

Barcode: 8054529025732



Made in China