

CABLE FIXATION 8XM12 BLACK

To lock the plug position of actor / sensor cables

Cable fixation 8× M12
Cable diameter (4...7 mm)

[Link to Product](#)

Illustration



Product may differ from Image

Commercial data

ECLASS-6.0	27069290
ECLASS-6.1	23140390
ECLASS-7.0	23140390
ECLASS-8.0	23140390
ECLASS-9.0	23140315
ECLASS-10.1	23140390
ECLASS-11.1	23140315
ECLASS-12.0	23140315
ETIM-5.0	EC001583
customs tariff number	39269097
GTIN	4048879458115
Packaging unit	1

Mechanical data

Reusability on/off min. 20 Cycles

Mechanical data | Material data

Color housing	black
Material housing	Plastic

Mechanical data | Mounting data

Clamping range min.	4 mm
Clamping range max.	7 mm
Height	11,5 mm
Width	45 mm
Depth	104 mm
Scanning mass	25×30 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	60 °C
