

## FullHD WiFi IP PT Indoor Camera TX-146

Rotatable camera head for optimal indoor all-round visibility



**2MP** FullHD  
1920x1080

**8m** Motion  
Tracking

**8m** 6 IR LED  
(850nm)

**Horizontal 90°  
& Vertical 55°**

**Free Security  
Premium App**

**Rotation  
355° & 130°**

**Wifi  
2.4GHz**

**MicroSD  
Storage**



- Ideal for monitoring indoor areas
- FullHD video resolution with max. 15fps
- Supports wifi up to ~10m in open areas
- Live monitoring via free iOS & Android app (worldwide)
- Motion detection & motion tracking
- Swivels horizontally and vertically (355° & 130°)
- Alarm function (push message) on your Smartphone
- Built-in microphone & speaker for 2-way communication
- H.264/H.265 video compression (for space-saving recordings of high quality)
- Automatic overlay loop recording
- Day / Night mode: built-in IR-CUT filter automatic switching
- 6 infrared LEDs for up to 8m night vision (850nm)

### Technical Specifications:

- Colour sensor: 1/ 2.9" CMOS (2 MP)
- Minimum illumination: 0.1 Lux @ (F2.0, AGC ON), 0 Lux with 6x IR LED
- Lens / Shutter: f=3.6mm / 1/50(1/60)s ~1/100000s
- Supports MicroSD(HC/XC) cards up to 128GB (FAT32/ exFAT) class10
- File size (night; B/W): 4MB/min (32GB = 5.5 days continuous recording);
- File size (day; colour): 6.4MB/min (32GB = 3.5 days continuous recording)
- Network Interface: 2.4GHz WiFi; Radiated output power max. 100mW
- Power supply: DC 5V±10% 1.5A; Power consumption 5W maximum
- Operating conditions: -10°C~+50°C, humidity 90% or less (non-condensing)
- Weight / Dimension: 192g / (H) 10.5 x Ø 8.0

**APP "Security Premium":** iOS 9.0 or above; Android 7.0 or above / EN, DE, FR, ES, IT, NL, SE, DK, NO, FI, CZ, PO (06-2020)

### Package Contents:

FullHD WiFi IP PT Indoor Camera TX-146, 1x USB power adapter 5V/1.5A, 1x USB-to-Micro-USB power cable (2m), 2x Screws & Dowels, 1x reset pin, 1x mounting bracket with screw, User Manual (short)

Article No. 4882



Compatible with:

4260358124100 / Article-No. 4880