

## HD Outdoor Camera with LED Lamp TX-106

Stand alone device powered by batteries



**HD 720** Video Recording  
HD 720p with sound

**FMP** Photo resolution  
1280x720 Pixel

**Battery** Operating with  
Batteries

**Wrench** Various Mounting  
Possibilities

**7m** PIR Sensor  
60° Angle

**Light** LED Light with  
150 Lumen

**Timer** Triggering Time  
1-1.5 seconds

**MicroSD** MicroSD Card  
up to 32GB

**IP65** Protection  
Class IP65

- Multi functional: video recording with sound, photo, light
- PIR motion detection of 60° angle up to ~7m (open areas)
- PIR trigger time 1-1.5 seconds
- LED light with 150 lumen brightness (2W) up to ~8m distance (open areas)
- LED indicator at low battery power
- Wall mounting (360° rotation, 180° up/down)
- Other mounting possibilities e.g. in the garden with the ground mounting holder
- Protection class IP65 (dust and waterproof)

### Technical Specifications:

- Video format: 720p, 25fps / Video file: MP4
- Photo format: 1280x720 pixel / Photo file: JPEG
- Camera lens: F=2.0, FOV 92° / 92°
- Luminous time ~20 seconds
- Storage: MicroSD\* card up to 32GB (Class10) [\*not included]
- Up to approx. 11.5 weeks of recordings on 32GB (20 recordings each 20MB per day)
- Power supply: 4x D-cell alkaline batteries\* 1.5V [\*not included]
- Ø duration battery life: Video mode 20x at night ~2.5 month / Photo mode 20x at night ~7 month / Light mode 20x at night ~2 month
- Operation temperature -10°C up to +40°C
- Weight / Dimensions: 400g / (L) 19.5 x (W) 15.0 (H) 10.5cm

### Package Contents:

- HD Outdoor camera with LED lamp TX-106
- 1x Wall mounting holder
- 1x Ground mounting holder
- 3x Screws with dowels
- User Manual

Article-No. 4757

