



**NEW**

# TTR-8634

STAND ALONE 33-45-78 RPM TURNTABLE WITH FM RADIO, LINE OUT AND HEADPHONES OUT. BUILT-IN AMPLIFIER AND SPEAKERS.

**BUILT-IN AMPLIFIER AND SPEAKERS**



**PORTABLE AUDIO**

# TTR-8634

STAND ALONE 33-45-78 RPM TURNTABLE WITH FM RADIO, LINE OUT AND HEADPHONES OUT. BUILT-IN AMPLIFIER AND SPEAKERS.



## CD PLAYER

Loader type
Electronic Shock Protection
Compressed audio playback
Disc support
Auto ID3 tag detection
MP3 search by
Data rate system
Fast forward / reverse
Track search
Intro scan
Random play
Repeat track / album
Program function

## TUNER

Tuner type	Analog
Ranges (band)	FM
RDS system / Radiotext	
Preset stations	
Stereo / Mono selector	•
Automatic tuning	
Manual tuning	•

## CASSETTE

Cassette deck
Cassette mechanism
Automatic Level Control (ALC)
One Touch Recording (OTR)
Built-in microphone

## USB/SD/MMC

Encoding
Playback
Copy
Delete
iPod compatibility

## TURNTABLE

R.P.M.	33/45/78
Tone Arm Mechanism	Autostop

## CONNECTIONS

Bluetooth	
USB port	
Card slot	
Aux in	
Line Out	• 2 x RCA
Headphones socket	Ø 3.5mm Jack

## AUDIO

Speaker system	2 speakers
Total PMPO Output Power	19 Watt
Nominal Output Power	2 x 1.2 Watt RMS
Volume control	Manual
Equaliser	

## GENERAL

Accessories included	AC/DC adaptor 45 RPM Adaptor
Colour Versions	Black
Display / Illumination	
Power supply	220V/12V AC/DC adaptor
Battery Memory	
Weight	1,77 Kg
Dimensions (WxLxH)	310x290x125mm

## COMMERCIAL

Container load 40'	3500 pcs
Container load 20'	1600 pcs
Shipping carton	2 pcs
Gift Box size (WxLxH)	154X335X326mm
Shipping car. size (WxLxH)	343X317X336mm
<b>EAN code</b>	<b>7621800032904</b>

<b>Master Carton EAN code</b>	<b>7621800054807</b>
-------------------------------	----------------------

Country of origin	P.R.C.
-------------------	--------