

Roadstar®

NEW

HRA-1500D+

VINTAGE STYLE HOME RADIO WITH DAB+ AND FM TUNER, AUX-IN AND HEADPHONES OUT.

DAB+
Digital Audio Broadcasting



HOME RADIO

HRA-1500D+

VINTAGE STYLE HOME RADIO WITH DAB+ AND FM TUNER, AUX-IN AND HEADPHONES OUT.



CD PLAYER

Loader type	
Electronic Shock Protection	
Compressed audio playback	
Disc support	
Auto ID3 tag detection	
MP3 search by	
Data rate system	
Fast forward / reverse	
Track search	
Intro scan	
Random play	
Repeat track / album	
Program function	

TUNER

Tuner type	Digital
Ranges (band)	DAB+ / FM
RDS system / Radiotext	•
Preset stations	20 + 20
Stereo / Mono selector	
Automatic tuning	•
Manual tuning	•

CASSETTE

Cassette deck	
Cassette mechanism	
Automatic Level Control (ALC)	
One Touch Recording (OTR)	
Built-in microphone	

USB/SD/MMC

Encoding	
Playback	
Copy	
Delete	
iPod compatibility	

TURNTABLE

R.P.M.	
Tone Arm Mechanism	

CONNECTIONS

Bluetooth	
USB port	
Card slot	
Aux in	Ø 3.5mm Jack
Line Out	
Headphones socket	Ø 3.5mm Jack

AUDIO

Speaker system	1 speaker
Total PMPO Output Power	16 Watt
Nominal Output Power	1 x 2 Watt RMS
Volume control	Encoding
Preset equaliser	•

GENERAL

Accessories included	AC / DC adaptor
Colour Versions	Wood
Display / Illumination	LCD / Amber
Power supply	DC 6V = 1A
Battery Memory	
Weight	2 Kg
Dimensions (WxLxH)	305x145x210 mm

COMMERCIAL

Container load 40' HQ	
Container load 40'	2'100 pcs
Container load 20'	1'440 pcs
Shipping carton	4 pcs
Gift Box size (WxLxH)	375x182x259 mm
Shipping car. size (WxLxH)	383x372x528 mm

EAN code

HRA-1500D+	7621800032775
Master Carton EAN code	
HRA-1500D+	7621800054685
Country of origin	P.R.C.