



**NEW**

# HRA-590D+/SL

DAB+/FM RADIO , LCD 2.8" TFT COLOR DISPLAY,  
DUAL ALARM, SLEEP TIMER, 3,5MM STEREO  
HEADPHONE JACK, AUX IN



**PORTABLE AUDIO**

# HRA-590D+/SL

DAB+/FM RADIO , LCD 2.8" TFT COLOR DISPLAY, DUAL ALARM, SLEEP TIMER, 3,5MM STEREO HEADPHONE JACK, AUX IN



## CD PLAYER

Loader type
Electronic Shock Protection
Compressed audio playback
Disc support
Auto ID3 tag detection
MP3 search by
Data rate system
Fast forward / reverse
Track search
Intro scan
Random play
Repeat track / album
Program function

## TUNER

Tuner type	DIGITAL
Ranges (band)	DAB+/FM
RDS system / Radiotext	•
Preset stations	40 DAB + 40 FM
Stereo / Mono selector	•
Automatic tuning	•
Manual tuning	•

## CASSETTE

Cassette deck
Cassette mechanism
Automatic Level Control (ALC)
One Touch Recording (OTR)
Built-in microphone

## USB/SD/MMC

Encoding
Playback
Copy
Delete
iPod compatibility

## TURNTABLE

R.P.M.
Tone Arm Mechanism

## CONNECTIONS

Bluetooth	
USB port	
Card slot	
Aux in	Ø 3.5mm Jack
Line Out	
Headphones socket	Ø 3.5mm Jack

## AUDIO

Speaker system	1 speaker
Total PMPO Output Power	8 Watt
Nominal Output Power	1x1 Watt RMS
Volume control	Digital
Equaliser	

## GENERAL

Accessories included	230V AC/DC 5V 1A ADAPTOR
Colour Versions	MATT BLACK WITH SILVER METAL GRILL
Display / Illumination	2.8" color DISPLAY
Power supply	230V AC/DC 5V 1A ADAPTOR 4x1.5 AA batt. (NOT INCL.)

Battery Memory	
Weight	0,54 Kg
Dimensions (WxLxH)	216x51x133mm

## COMMERCIAL

Container load 40'	5701 pcs
Container load 20'	4240 pcs
Shipping carton	10 pcs
Gift Box size (WxLxH)	309x98x181 mm
Shipping car. size (WxLxH)	507x320x378 mm

<b>EAN code</b>	<b>7621800032959</b>
<b>Master Carton EAN code</b>	<b>7621800054845</b>
Country of origin	P.R.C.