

Roadstar®

NEW

HRA-1345NUSWD

RETRO STYLE FM HOME RADIO WITH USB PORT,
SD CARD READER AND AUX-IN.
DISPLAY AND KNOBS WITH BLUE LIGHT.



HOME RADIO

HRA-1345NUSWD

RETRO STYLE FM HOME RADIO WITH USB PORT, SD CARD READER AND AUX-IN. DISPLAY AND KNOBS WITH BLUE LIGHT.



CD PLAYER

Loader type	
Electronic Shock Protection	
Compressed audio playback	
Disc support	
Auto ID3 tag detection	
MP3 search by	
Data rate system	
Fast forward / reverse	
Track search	
Intro scan	
Random play	
Repeat track / album	
Program function	

TUNER

Tuner type	Analog
Ranges (band)	FM
RDS system / Radiotext	
Preset stations	
Stereo / Mono selector	
Automatic tuning	
Manual tuning	•

CASSETTE

Cassette deck	
Cassette mechanism	
Automatic Level Control (ALC)	
One Touch Recording (OTR)	
Built-in microphone	

USB/SD/MMC

Encoding	
Playback	•
Copy	
Delete	
iPod compatibility	

TURNTABLE

R.P.M.	
Tone Arm Mechanism	

CONNECTIONS

Bluetooth	
USB port	•
Card slot	• (SD card)
Aux in	Ø 3.5mm Jack
Line Out	
Headphones socket	

AUDIO

Speaker system	1 speaker
Total PMPO Output Power	16 Watt
Nominal Output Power	1 x 2 Watt RMS
Volume control	Analog
Preset equaliser	

GENERAL

Accessories included	
Colour Versions	Wood and Silver
Display / Illumination	Blue
Power supply	AC 230 V, 50Hz

Battery Memory

Weight	1 Kg
Dimensions (WxLxH)	225x145x135 mm

COMMERCIAL

Container load 40'	5'900 pcs
Container load 20'	2'940 pcs
Shipping carton	4 pcs
Gift Box size (WxLxH)	270x210x175 mm
Shipping car. size (WxLxH)	415x275x335 mm

EAN code

HRA-1345NUSWD	7621800032355
---------------	---------------

Master Carton EAN code

HRA-1345NUSWD	7621800054326
Country of origin	P.R.C.