



TRA-2235

PORTABLE FM RADIO WITH
HEADPHONES OUT.



TRA-2235/BK



TRA-2235/RD

PORTABLE RADIO

TRA-2235

PORTABLE FM RADIO WITH
HEADPHONES OUT.



CD PLAYER

Loader type
Electronic Shock Protection
Compressed audio playback
Disc support
Auto ID3 tag detection
MP3 search by
Data rate system
Fast forward / reverse
Track search
Intro scan
Random play
Repeat track / album
Program function

TUNER

Tuner type	Analog
Ranges (band)	FM
RDS system / Radiotext	
Preset stations	
Stereo / Mono selector	(Mono)
Automatic tuning	
Manual tuning	•

CASSETTE

Cassette deck
Cassette mechanism
Automatic Level Control (ALC)
One Touch Recording (OTR)
Built-in microphone

USB/SD/MMC

Encoding
Playback
Copy
Delete
iPod compatibility

TURNTABLE

R.P.M.
Tone Arm Mechanism

CONNECTIONS

Bluetooth	
USB port	
Card slot	
Aux in	
Line Out	
Headphones socket	Ø 3.5mm Jack

AUDIO

Speaker system	1 speaker
Total PMPO Output Power	6.4 Watt
Nominal Output Power	1 x 0.8 Watt rms
Volume control	Analog
Equaliser	

GENERAL

Accessories included	AC Cable
Colour Versions	BK - Black RD - Red

Display / Illumination	
Power supply	230V AC / 4 x "LR6" Batteries

Battery Memory	
Weight	0.5 Kg
Dimensions (WxLxH)	210x20x120 mm

COMMERCIAL

Container load 40'	15'448 pcs
Container load 20'	8'000 pcs
Shipping carton	12 pcs
Gift Box size (WxLxH)	225x100x130 mm
Shipping car. size (WxLxH)	625x235x280 mm

EAN code

TRA-2235/BK	7621800031617
TRA-2235/RD	7621800031624

Master Carton EAN code

TRA-2235/BK	7621800053442
TRA-2235/RD	7621800053459
Country of origin	P.R.C.