

KERN 346-78

KERN

Individual weight, OIML Class M1, 20 kg, Block Eco, cast iron lacquered



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	346

Measuring System

Test weight - volume (cm ³)	2816,9014
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m ³)	600
Test weight - volume uncertainty (cm ³)	238,048
Weight OIML class	M1
Test weight - nominal value	20 kg
Permissible tolerance according to OIML (+/-)	1 g
Test weight - Density (kg/m ³)	7100
OIML-compliant	✓
Test weight - Density [Min] (OIML)	3000

Construction

Shape weight	Block Eco
Dimensions weight (W×D×H)	231×117×143 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-645
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	240×130×160 mm
Shipping method	Parcel service
Net weight approx.	20 kg
Gross weight approx.	20 kg
Shipping weight	20 kg

Optional cases

Case - Aluminium article number	346-080-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761241695
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

