

KERN 356-76

KERN

Individual weight, OIML Class M2, 5 kg, Block Eco, cast iron lacquered



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	356

Measuring System

Test weight - volume (cm ³)	704,2254
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m ³)	600
Test weight - volume uncertainty (cm ³)	59,512
Weight OIML class	M2
Test weight - nominal value	5 kg
Permissible tolerance according to OIML (+/-)	800 mg
Test weight - Density (kg/m ³)	7100
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300

Construction

Shape weight	Block Eco
Dimensions weight (W×D×H)	150×75×84 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-643
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	150×75×84 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	5,0 kg
Shipping weight	5 kg

Optional cases

Case - Aluminium article number	346-060-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761241756
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

