

KERN 356-77

Individual weight, OIML Class M2, 10 kg, Block Eco, cast iron lacquered

KERN

Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	356

Measuring System

Test weight - volume (cm ³)	1408,4507
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m ³)	600
Test weight - volume uncertainty (cm ³)	119,024
Weight OIML class	M2
Test weight - nominal value	10 kg
Permissible tolerance according to OIML (+/-)	1,6 g
Test weight - Density (kg/m ³)	7100
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300

Construction

Shape weight	Block Eco
Dimensions weight (W×D×H)	190×95×109 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-644
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	190×95×109 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg

Optional cases

Case - Aluminium article number	346-070-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761241794
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

