KERN **356-79**

Individual weight, OIML Class M2, 50 kg, Block Eco, cast iron lacquered



Category

Brand	KERN
Product categoriy	Individual weight
Product group	OIML M2
Product family	356

Measuring System

Test weight - volume (cm^3)	7042,2535
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m^3)	600
Test weight - volume uncertainty (cm^3)	595,12
Weight OIML class	M2
Test weight - nominal value	50 kg
Permissible tolerance according to OIML (+/-)	8 g
Test weight - Density (kg/m^3)	7100
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300

Construction

Shape weight	Block Eco
Dimensions weight (W×D×H)	310×155×192 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-646

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	310×155×192 mm
Shipping method	Freight
Net weight approx.	50 kg
Gross weight approx.	50 kg
Shipping weight	50 kg

Product information

GTIN/EAN number	4045761241817
REACH classification	no prohibited substances

Pictograms

STANDARD

2 DAYS

OPTION

DAkkS