

SAUTER BSWA-01

KERN

Adjustment device for regular adjustment of the sound level meter



Category

Brand	Sauter
Product category	Measurement technology
Product group	Accessories for sound level measurement

Measuring System

Sound level meter class	Class 1 Class 2
Frequency range [Max]	1010 Hz
Sound level [Min] (db)	94 dB
Sound level [Max] (db)	114 dB
Frequency range [Min]	990 Hz
Units	dB
Tolerance (% of [Max])	0,2%

Construction

Dimension housing (W×D×H)	70×70×50 mm
Dimensions completely mounted (W×D×H)	70×70×50 mm
Material housing	plastic

Power Supply

Supplied power supply	Battery
Battery / accumulator type	Alkali(-Manganese)
Battery connection	Pad + Spring
Battery capacity	3.000 mAh
Battery voltage	3 V
Battery - Number of cells	2
Battery - Individual weight	46 g
Battery - Total weight	92 g
Battery - Construction	Individual cells
Battery capacity (Wh)	4,5 Wh

Environmental conditions

Use temperature [Min]	-10 °C
Use temperature [Max]	50 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-291
Article number for factory calibration	961-291

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	145×105×70 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,25 kg
Shipping weight	0,245 kg

Product information

GTIN/EAN number	4045761220201
REACH classification	no prohibited substances

Pictograms

STANDARD

