

KERN FOB 3K-4NL

KERN

Stainless steel bench scale with large weighing ranges and IP65 protection against dust and water spray



Category

Brand	KERN
Product category	Industrial scale
Product group	Stainless steel bench scale
Product family	FOB-NL

Measuring System

Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	3000 g
Readability [d]	0,2 g
Reproducibility	0,2 g
Linearity	± 0,6 g
Resolution	15.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	3 kg (M1)
Possible calibration points	3 kg
Stabilization time	2 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	1 g
Construction type of the scale	Single-range balance
Units	g lb
Maximum creep (15 minutes)	800 mg
Maximum creep (30 minutes)	1,6 g
Default unit	g

Display

Display type	LCD
Display backlight	no

Display digit height	25 mm
----------------------	-------

Construction

Dimension housing (W×D×H)	285×255×90 mm
Dimensions weighing surface (W×D)	252×200 mm
Dimensions weighing surface	252×200 mm
Material housing	stainless steel
Material weighing plate	stainless steel

Functions

IP protection - complete device	IP65
Auto-off interval(s) in battery mode/rechargeable battery mode	2 min
Tare function	manual (multi)

Power Supply

Supplied power supply	Battery
Plug-in power supply / adapter for countries - included with the delivery	EURO CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	230 V AC, 50 Hz
Input voltage device / power [Max]	15 V, 500 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm, Ø outside 5,5 mm, long 12 mm
Battery / accumulator type	Alkali(-Manganese)
Battery	4×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	48 h
Battery voltage	6 V
Battery - Individual weight	92 g
Battery/Accu connected	not connected, enclosed

Environmental conditions

Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Min]	25 %
Humidity of environment [Max]	95 %

Approval

CE mark	✓
---------	---

KERN FOB 3K-4NL



Stainless steel bench scale with large weighing ranges and IP65 protection against dust and water spray

Services (optional)

Article number for adjustment at the location of installation	961-247
Article number for DAkkS calibration	963-127
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	420×350×175 mm
Shipping method	Parcel service
Net weight approx.	3,8 kg
Gross weight approx.	4,4 kg
Shipping weight	5,1 kg

Product information

GTIN/EAN number	4045761214361
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

