

# KERN OBB-A3200

Eyepiece: WF 10x / Ø 18 mm, anti-fungus

# KERN

## Pictograms

### STANDARD



## Category

|                  |                     |
|------------------|---------------------|
| Brand            | Optics              |
| Product category | Optical Instrument  |
| Product group    | Microscope eyepiece |

## Construction

|                   |             |
|-------------------|-------------|
| Dimension (W×D×H) | 55×30×30 mm |
|-------------------|-------------|

## Ocular

|                       |          |
|-----------------------|----------|
| Ocular field width    | WF       |
| Eye point             | Standard |
| Ocular magnifications | 10x      |
| Ocular visual field   | 18 mm    |
| Ocular diameter       | 23,2 mm  |

## Environmental conditions

|                           |       |
|---------------------------|-------|
| Storage temperature [Min] | -5 °C |
| Storage temperature [Max] | 40 °C |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 85×65×45 mm    |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,10 kg        |
| Gross weight approx.         | 0,40 kg        |
| Shipping weight              | 0,4 kg         |

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761237391            |
| REACH classification | no prohibited substances |

