

KERN OZB-A5 133



Individuality, variety and flexible working through our modular construction system ► ECO-Universal stands



Plug-in power supply / adapter for EURO countries - optional
UK

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	385×370×330 mm
Shipping method	Parcel service
Net weight approx.	3,0 kg
Gross weight approx.	4,2 kg
Shipping weight	9,4 kg

Product information

GTIN/EAN number	4045761232167
REACH classification	no prohibited substances

Pictograms

STANDARD



Category

Brand	Optics
Product category	Optical Instrument
Product group	Stereo Microscope- Stand

Construction

Dimension (W×D×H)	283×292×303,5 mm
-------------------	------------------

Illumination

Illuminance	Reflected light Transmitted light
Illumination type incident light	LED
Illumination type transmitted light	LED
Illumination intensity incident light	3 W
Illumination intensity transmitted light	3 W

Focussing

Focusing mechanism	coaxial coarse and fine drive
--------------------	-------------------------------

Stereomicroscope stand

Stand type	pillar form
Column height	303,5 mm
Diameter mounting universal stand (Ø)	25 mm
Diameter mounting microscope head (Ø)	76 mm

Power Supply

Supplied power supply	Power supply unit
-----------------------	-------------------