



Discover more details and matching accessories online!

Stainless steel platform scales with IP65/67 protection, also with XL platform or optional verification

Features

- Ideal for the robust industrial applications
- Display device: stainless steel, protection against dust and water splashes IP65, (only when using rechargeable battery pack)
- Platform: made entirely of stainless steel, silicone-coated Stainless Steel load cell, protection against dust and water splashes IP67
- **1** KERN SFB-H: Column, standard, for models with weighing plate size
 - A** Height of stand approx. 200 mm
 - B** Height of stand approx. 400 mm

Technical data

- Large backlit LCD display, digit height 52 mm
- Dimensions of display device W×D×H 266×165×96 mm
- Weighing platform dimensions W×D×H, stainless steel
 - A** 300×240×107 mm
 - B** 400×300×111 mm
 - C** 500×400×120 mm
 - D** 650×500×139 mm

- Rechargeable battery pack integrated, as standard, operating time up to 35 h without backlight, charging time approx. 12 h
- Permissible ambient temperature -10 °C/40 °C

*Please note: only one optional interface can be fitted for each device

STANDARD



OPTION



FACTORY



SFB-M/
SFB-HM

Model	Weighing capacity [Max] kg	Readability [d] g	Verification value [e] g	Minimal load [Min] g	Weighing plate	Net weight approx. kg	Options	
							Verification	Calibr. Certificate
KERN							M KERN	DAkkS accr. KERN
SFB 50K-3XL	50	5	-	-	C	13	-	963-128
SFB 100K-2XL	100	10	-	-	D	24	-	963-129
1 with elevated display								
SFB 10K1HIP	10	1	-	-	A	8	-	963-128
SFB 20K2HIP	20	2	-	-	A	8	-	963-128
SFB 50K5HIP	50	5	-	-	A	8	-	963-128
SFB 50K5LHIP	50	5	-	-	B	10	-	963-128
SFB 100K10HIP	100	10	-	-	B	10	-	963-129
Note: For devices that require verification (conformity assessment according to NAWI 2014/31/EU), please include the verification when placing your order. The initial verification is not possible after delivery. Please inform the full address of the location of use for the initial verification.								
SFB 60K-2XLM**	60	20	20	400	C	14	965-229	963-129
SFB 100K-2LM**	150	50	50	1000	C	14	965-229	963-129
SFB 100K-2XLM**	150	50	50	1000	D	24	965-229	963-129
1 with elevated display								
SFB 100K-2HM**	150	50	50	1000	B	10	965-229	963-129
SFB 15K5HIPM**	15	5	5	100	A	8	965-228	963-128
SFB 30K10HIPM**	30	10	10	200	A	8	965-228	963-128
SFB 60K20LHIPM**	60	20	20	400	B	10	965-229	963-129

1 **ONLY WHILE STOCKS LAST