




RoHS Compliant



Pin Assignment



Electrical Test:

- 1.100% TEST OPEN SHORT MIS-WIRE.
- 2.CONTACT RESISTANCE:3Ω MAX.
- 3.INSULATION RESISTANCE:5MΩ MIN.
- 4.HI-POT:300V DC/10MS.
- 5.SUPPORT USB2.0 480Mbps.

D		
C		
B	更新彩盒档案/更正Model No	2021-05-14
VER.A	REVISE	DATE

Company: CONRAD

Item	2347572	
Draw	<i>Kobe</i>	Date: 2020.10.10
Approval		
Duty	F16	BOM.NO:14122

D		45P PVC BLACK(Anti-microbial)		G
C	1	TYPE C M Solder Type (Black Insulator,Nickel plated)Stamping metal shell+R(56K)	1	PCS
B		USB AM(White Insulator,Nickel plated)	1	PCS
A		UL2725 30#*1P+30#*1C+22#*1C+26#*4D+AL, OD=4.2mm BLACK PVC JACKET(Anti-microbial)	1	PCS
NUMBER	BOM.NO	PRODUCT SPECIFICATIONS	Quantity	Unit