

## CAN cable 2.0 m (D-Sub male to female)



The CAN cable is ideal suited for connection of CAN and CAN FD components. It is 2.0 m long, shielded and has twisted wires.

The cable can also be used in CAN FD buses.

### FEATURES AND BENEFITS

- All pins connected (1-to-1)
- Length 190 cm (cable); total length 200 cm
- 9-pin D-Sub plug to 9-pin D-Sub socket
- Shielded cable

<b>ORDER NUMBER</b>	<b>1.04.0076.00180</b>
CAN connector	D-Sub 9-pin, plug to socket
Pin allocation	1-to-1
Contact resistance	10 mOhm
Testing voltage	800 V
Rated voltage	350 V
Temperature range	0 °C to 70 °C
Length	200 cm

## PIN ALLOCATION

1	brown	1
2	red	2
7	orange	7
3	yellow	3
4	green	4
5	blue	5
6	purple	6
8	grey	8
9	black	9
Shield		Shield

## TECHNICAL DRAWING

