

Mini-Soundbar BT-X54











Mini Soundbar with Bluetooth V5.1

MicroSD-card, FM-radio, USB and AUX-IN modes Pairing with Bluetooth-enabled audio devices, Smartphones, Tablets, etc.

Listen to MP3-player, CD or other devices without BT via audio cable (3.5mm)

USB media play-back for up to 128GB 10W speakers with passive bass radiator

Technical specifications:

• Bluetooth: BT Version V5.1 Transmitting distance <10m (open space) Frequency band 2.4GHz Radiated transmission power max. 2.5mW



- Modes: FM / BT / USB flash drive / MicroSD-card / AUX-IN
- FM frequency band: 87.5-108MHz
- USB / MicroSD capacity supporte: dUp to 128GB
- Music format: MP3 / WAV
- AUX-connector: 3.5mm
- SNR>85dB
- Battery: Built-in Lithium-ion battery 1800mAh, 3.7V
- Charging time: 2-3 hours (5V, 2A)
- Playing time: 3 hours (with 50% volume), 1.5 hours (with 100% volume)
- Power input: DC 5V / 2A
- Operating temperature: 0°C up to +40°C
- Material: PC / ABS / metal mesh
- Weight / dimension: 584g / (L) 39.5 x (W) 5.5 x (H) 7.2cm

Package Contents:

MusicMan BT-X54, AUX cable, charging cable, user manual

