

DAB+ Soundbar TX-139



Soundbar with DAB+ & FM-radio, Bluetooth V5.0, optical output, HDMI ARC, USB and AUX-IN
Pairing with Bluetooth-enabled audio devices, Smartphones, Tablets, etc.

USB media play for up to 64GB

DAB+/FM coaxial antenna included

LED effect light with 7 selectable colours

Illuminated LCD display (2,7x1,5cm)

Clock & Alarm function

Remote control

Technical specifications:

- Bluetooth:
 - BT Version V5.0
 - Transmitting distance <10m (open space)
 - Frequency band 2.4GHz
 - Radiated transmission power max. 2.5mW

- Modes: DAB + / FM / BT / USB flash disk / HDMI ARC / optical out / AUX-IN
- FM frequency band: 87.5-108MHz
- DAB+ frequency band: 170-240MHz
- USB capacity: Up to 64GB
- Music format: MP3 / WAV
- AUX-connector: 3.5mm
- Loudspeaker / frequency / impedance: 4x10W Ø57mm / 100Hz-20kHz / 4Ω
- SNR / DAB+ sensitivity: ≥80db / -101dB
- Power input: DC 18V / 3A
- Operating temperature: 0°C up to +40°C
- Material: PC / ABS / Texture mesh
- External antenna: SMA connector, length: 2m
- Weight / dimension:
 - 1.9kg / (L) 100.0 x (W) 7.5 x (H) 7.5cm

Package Contents:

Technaxx® DAB+ Bluetooth Soundbar TX-139, AC adapter, AUX cable, DAB+ antenna, remote control, user manual



Article No. 4853

