

## Laser Rangefinder TX-152 with speed measurement function



-  Range up to 600m
-  6 times magnification
-  Speed detection
-  Splash water proof
-  Diopter compensation
-  Golf mode















- Measuring range up to 600m
- 6 times magnification
- Focus adjustable
- Golf mode (pin seeker)
- Speed measurement mode
- Accuracy +/- 1m
- With tripod socket

### Technical specifications:

- Laser type: Class1
- Wavelength: 905nm
- Lens diameter: 16mm
- Exit pupil diameter: 3.8mm
- Measuring range of distance: 5-600m
- Measuring range of speed: 0-300km/h
- Magnification: 6 times
- IP-Class: IP 54
- Precision of distance measure: ±1m
- Precision of speed measure: ±5km/h
- Operation temperature: 0°C to 40°C
- Battery: 2x AAA battery, 1.5V
- Weight / Dimensions: 172g / (L) 105 x (W) 82 x (H) 43mm

### Package Contents:

Technaxx TX-152, 2x AAA batteries, belt bag, hand rope, cleaning cloth, user manual



Article No. 4899

