

XXXL - Bowl
10 liter capacity for
max. 6 - 6.5 kg dough
preparation

**Long-life professional
motor (1500 W)**

**Long-life professional
metal gear**

**Splash guard lid with
refill opening**



Without decoration



NEW! Kneading machine
KM 3765

- Robust kneading machine with resistant metal gear
- 8 speed levels (0/1/2/3/4/5/6 + pulse)
- Extra-large 10 litre stainless steel bowl for max. 6–6.5 kg dough preparation
- High-performance long-life professional motor (1500 watt)
- Consistent performance due to load-dependent electronic rotation speed control
- Aluminium die-cast kneading hooks for heavy dough like yeast dough, bread dough or pasta dough
- Aluminium die-cast stirring hook for light dough like short pastry dough, crumble dough or sponge mixture
- Stainless steel whisk for whipping

- of egg white, cream, meringue and many others
- 35° swivelling multi-purpose arm
- Unlocking mechanism for multi-purpose arm
- Safety circuit – machine stops when lifting the arm
- Rotary switch (white illuminated)
- High quality chrome application
- Transparent splash guard lid with refill opening
- Soft start for slow mixing
- Easy to operate and to clean
- High stability due to suction feet
- Quick-action chuck for holding the tools
- 220–240 V, 50/60 Hz, 1500 W



Stainless steel whisk



Aluminium die-cast dough hook



Aluminium die-cast stirring hook



35° swivelling multifunction arm



Rotary switch (white illuminated)

Color:	Red
Article no.:	263 958
Article EAN-Code:	4 006 160 639 582
Exportpack EAN-Code:	4 006 160 556 636
Color:	Titan
Article no.:	263 957
Article EAN-Code:	4 006 160 639 575
Exportpack EAN-Code:	4 006 160 556 629
PU:	1 piece
20"/40"/HQ Container:	487 / 999 / 1129

Dimensions	(approx. W x H x D) and weight
Unit:	413 x 387 x 268 mm; 6,39 kg
Box:	435 x 430 x 288 mm

CTC Clatronic International GmbH
Industriering Ost 40
47906 Kempen