

# SENOA



## PG 8117 SENOA BOOST S

---

### USP at a glance:

- no risk of burns. SafeTouch housing eliminates the danger of burns on all surfaces
- rapid grill-start: from 0 to 500°C in just 10 minutes
- BoostZone: 500°C for perfect brandigts. Double-heating technology for maximum power
- stable stand with storage tray
- also usable as a table grill



500 °C BOOST ZONE INDOOR & OUTDOOR XXL POWER CORD SAFE TOUCH ECO FRIENDLY

## Productdetails



Many removable parts allow easy cleaning



Single heater: temperatures up to 500°C



SafeTouch housing eliminates the danger of burns



Water in reflection tray: for easy cleaning, against smoke and odour.



BoostZone: Double-heating technology for maximum power

## Important data

Power in watts	3000 W
Colour/Material	Stainless steel-black
Special features	- Safety microswitch - Heating element switches off automatically when removed
Supply cable length	2,0 m
Grill temperature	up to 500°C
Dimensions of the grill surface	approx. 41.5 x 24 cm (approx. 996 cm <sup>2</sup> )
Unit dimensions without base frame (H x W x D in cm)	62,0 x 24,0 x 41,0
Appliance dimensions with stand (H x W x D in cm)	62,0 x 91,0 x 50,0
Packaging dimensions (H x W x D in cm)	80,5 x 29,7 x 45,5
Net weight / gross weight (in kg)	6.5 kg / 9.8 kg
GTIN code	400 814 603 4572