

Desk calculators



DF-120EM

Functions

Calculation functions

- Currency conversion
- Pro-percentage
- Mark up with percentage key
- Cost/sell/margin
- Backspace key
- Sign change (+/-)
- Rounding selector
- Key rollover

Memory

- Grand total memory
- 3-key memory

Product features

Display

- 12-digit display
- LC display
- Function command signs
- 3-digit comma markers

Power

- Solar/Battery powered
- Backup battery
- Auto power off

Input

- Double zero key

Materials / Outer Appearance

- Plastic keys
- Aluminum panel
- Shock absorbing keys
- Rubber feet
- Ergonomically shaped keys



126 x 31 x 179 mm



180 g

4549526609947
EAN Code

www.casio-europe.com

CASIO

Technical changes and errors excepted. The image sizes do not correspond to the original sizes. The colors may differ slightly from the original.

Desk calculators



DF-120EM

Operating instructions for selected functions

PROFESSIONAL PERCENTAGE CALCULATION

Addition of 10% to the reference value 50 with interim display of the amount to be added during the calculation.

50 × 10 %

5

+

55

Subtraction of 10% from the reference value 50 with interim display of the amount to be subtracted during the calculation.

50 × 10 %

5

-

45

Pocket and desk calculators

Pro-percentage

Determine percentage-based surcharges and discounts with a separate display of the calculated value. Comfortable calculating percentage markups and markdowns and subsequent display of the calculated absolute value.

COST SELL MARGIN

The sales price of a product is €150. Determination of the purchase price if the margin is 30%.

150 SELL 30 MAR COST

105

Purchase price in €

The purchase price of a product is €105. Determination of the sales price if the margin is 30%.

105 COST 30 MAR SELL

150

Sales price in €

The purchase price of a product is €105. The sales price is €150. Determination of the margin: %/absolute.

105 COST 150 SELL MAR

30

Margin as a %

MAR

45

Absolute margin in €

Pocket and desk calculators

Cost/sell/margin

The profit calculation allows the determination of cost, selling price and margin. The simple entry and transparent display make commercial calculations in particular easier.

AUTOMATIC ROUNDING

F: All decimal places are displayed.

CUT: After the selected number of decimal places, all further ones are truncated.

UP: Rounding is always up, regardless of the value of the places after the decimal (varies by model, not always available).

5/4: Rounding down for 0, 1, 2, 3, 4 / Rounding up for 5, 6, 7, 8, 9

4/3/2/1: Number of decimal places desired for the rounding mode (varies by model).

ADD2: 2 decimal places are assumed in all additions/subtractions. The decimal point is set automatically. The last two numbers are interpreted as places after the decimal.

Optional rounding, for example 5/4: 2 decimal places

7 ÷ 9 =

0.78

Optional rounding down, for example CUT, 2 decimal places

7 ÷ 9 =

0.77

Optional rounding down, for example UP, 2 decimal places

7 ÷ 9 =

0.78

Optional addition aid ADD2

155 + 265 =

4.20

Pocket and desk calculators

Rounding selector

Individual definition of the rules for rounding.