



TECHNIRADIO 4 IR

DAB+ / FM / sleek Internet radio

EAN	Colour	Item no.	Weight (Box)	Weight	Device (W x H x D)	Box
4019588039278	schwarz/silber	0000/3927	1.05 kg	675 g	21.00 x 13.00 x 9.00 cm	28.00 x 18.00 x 12.00 cm

TOP FEATURES

DAB+ digital radio

FM radio (with RDS and PLL)

Limitless music variety via Internet radio

TFT colour display (2.4")

Date and time display

Two radio alarms available

Snooze and sleep function

Favoritenspeicher (40 für DAB+, 40 für UKW und 40 für Internetradio)

WLAN

WLAN : 802.11 a/b/g/n (2.4 GHz and 5 GHz bands are supported)

AMBIENT OPERATING CONDITIONS

Humidity : 5 - 90 % relative air humidity (non-condensing)

Ambient temperature : 5 - 35 °C

CONNECTIONS

Headphone connection jack (3,5mm) : 1

DISPLAY

Size : 2.4 Zoll

RadioVIS : Yes

Type : TFT colour display

Dimmable : Yes

Slide show/catSLS : Yes

HANDLING/COMFORT

Clock : Yes

Alarm : Yes

Sleep timer : Yes

Snooze : Yes

CONNECT app : Yes

Favourites programme manager DAB+ : 40

Favourites programme manager FM : 40

LOUDSPEAKERS

Mono speakers : Yes

Stereo speakers : Yes

Output performance : 3 W (RMS)

Equalizer : Yes

NETWORK & COMMUNICATION

Bluetooth : Yes

NFC : Yes

OTHER FEATURES

OSD languages : English, German, French, Polish, Italian, Dutch, Czech, Slovakian, Norwegian, Danish, Swedish, Finnish, Spanish, Turkish, Portuguese

POWER SUPPLY

Nominal voltage : 230 V

Frequency : 50 Hz

Mains adapter : 5V / 2.000mA

Type of power supply : External

RADIO / RECEPTION

DAB+ : 174 - 240 MHz

FM/RDS : 87.5 - 108 MHz

Internet radio : Yes

Aerial : DAB / FM telescopic aerial

RADIO TYPE

stationary radio : Yes

STREAMING

Spotify : Yes

Multiroom : Yes

Audio streaming : Yes

TECHNISAT CONNECT

Control : Yes

SCOPE OF DELIVERY

TECHNIRADIO 4 IR, power pack, user manual