

WALLBOX FOR ELECTRIC VEHICLE CHARGING



Can be installed on a stainless steel stand - stand not included



SPECIFICATIONS:

AWB1P32AT2NCB

AWB3P32AT2NCB

AC power:	1P+N+PE
Power supply Voltage:	AC230~±10%
Rated current:	10-32A
Frequency:	50-60Hz
Sockets/plugs:	Type2
Weight:	2.8kg
IP grade:	IP55/44
Working temperature:	-40°C ~ 45°C
Cooling way:	natural cooling
RCCB:	Type B

AC power:	3P+N+PE
Power supply Voltage:	AC400~±10%
Rated current:	10-32A
Frequency:	50-60Hz
Sockets/plugs:	Type2
Weight:	3.0kg
IP grade:	IP55/44
Working temperature:	-40°C ~ 45°C
Cooling way:	natural cooling
RCCB:	Type B

DISTRIBUTED BY:

BLP EV SYSTEMS APS - EDITHS ALLÉ 8, 5250 ODENSE SV, DENMARK