

NEMA17 GEAR STEPPER MOTOR

NEMA17-08GM



Our NEMA 17 series are very small high torque stepper motors that can reach speeds of up to 3000 rpm.

This compact stepper motor with a 4:1 transmission gearing is suitable for applications in which you require a precise and powerful working stepper motor.

MAIN FEATURES	
Shaft	Ø 5 x 19 mm (4.5 mm flat spot)
Interface connection	6 JST pin connector
Dimensions	43 x 43 x 75 mm
Items delivered	NEMA17 planetary gear stepper, connection cable


PERFORMANCE SPECIFICATIONS		
96%		
4:1		
3.5 Nm		
6 Nm		
15		
3000 RPM		
5000 RPM		
0.28 Nm		
5.12 V		
0.84 A		
1.8°±5%		
2		
6.1 Ω		
8.9 mH		
100 MΩ min. @500 V DC		
B (130 °C)		
38 g·cm²		
0.012 Nm		
-10 °C - 50 °C		

FURTHER DETAILS	
Article No.	NEMA17-08GM
EAN:	4250236821757
Customs Tariff No.	8501109990

www.joy-it.net SIMAC Electronics GmbH, Pascalstr. 8, 47506 Neukirch<u>en-Vluyn</u>



DRAWING



WIRING

