



NOTE:

1. Electrical test:
  - (1) 100% open short & miss wire test
2. RoHS 3.0 AND REACH COMPLIANT
3. PACKING: paperbag w/Renkforce sticker
4. Operation temperature: -10°C ~ +60°C  
 Storage temperature: -20°C ~ +75°C  
 Operation humidity: 10%~85%  
 Storage humidity: 10%~85%

MATERIAL LIST:

④	THUMB SCREW	#4-40*15 PLATED NICKEL	2	
③	MOLDED	45P BLACK PVC	1	
②	SCREW NUT	NUT-NICKEL PLATED #4-40	1	
①	CONNECTOR	P1+P2:RJ45 8P8C FEMALE+RJ45 8P8C FEMALE:GOLD FLASH CONTACTS, BLACK INSULATION	1	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK	CUSTOMER	ITEM NO.	2356101			
					PRODUCT NAME	CAT.6 UTP RJ45 F/F	UNO ITEM NO.	765002	UNIT	MM
		NEW	2021. 06. 16	A	DRAWNBY	CHECKBY	APPOBY	DATE		
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.				2021. 06. 16		