

<b>UN38.3 试验概要</b> <b>UN38.3 Test Summary</b>	
<b>样品信息</b> <b>Sample Information</b>	
样品名称 <b>Sample Name</b>	可充电锂离子电池组 Rechargeable Li-ion Battery
样品类型 <b>Sample Type</b>	锂离子电池组 Lithium ion battery
样品型号 <b>Sample Model</b>	GSP-1S3P-CH4A
规格参数 <b>Specifications</b>	3.6V 7500mAh 27Wh
锂含量 <b>Lithium Content</b>	--
产品质量 <b>Product Mass</b>	Approx 154.3g
物理描述 <b>Physical description</b>	方形 Prismatic 蓝黑杂色 Blue & Black
委托方 <b>Applicant</b>	广州鹏辉能源科技股份有限公司 Guangzhou Great Power Energy & Technology Co., Ltd.
委托方地址 <b>Applicant Address</b>	中国广东省广州市番禺区沙湾镇市良路（西村段）912号 NO.912, West Village Segment, Shiliang Road, Shawan Town, Panyu District, Guangzhou City, Guangdong Province 511483, P.R. China
制造商 <b>Manufacturer</b>	广州鹏辉能源科技股份有限公司 Guangzhou Great Power Energy & Technology Co., Ltd.
制造商地址 <b>Manufacturer Address</b>	中国广东省广州市番禺区沙湾镇市良路（西村段）912号 NO.912, West Village Segment, Shiliang Road, Shawan Town, Panyu District, Guangzhou City, Guangdong Province 511483, P.R. China
制造商电话 <b>Manufacturer Telephone</b>	020-39196888
制造商邮箱 <b>Manufacturer Email</b>	info@greatpower.net
制造商网址 <b>Manufacturer Website</b>	http://www.greatpower.net/
测试标准 <b>Test Standard</b>	《联合国关于危险货物运输的建议书 试验和标准手册》第38.3章第六版修订1 <United Nations Recommendations on the Transport of Dangerous Goods: Manual of Tests and Criteria> (ST/SG/AC.10/11/Rev.6/Amend.1 Section 38.3)

<b>UN38.3 试验概要</b> <b>UN38.3 Test Summary</b>		
<b>Reference to assembled battery testing requirements 集成电池组试验要求:</b> <input checked="" type="checkbox"/> 不适用 Not application <input type="checkbox"/> UN38.3.3(f) <input type="checkbox"/> UN38.3.3(g)		
条款Clause	测试项目Test Item	测试结果Test Results
38.3.4.1	高度模拟 Altitude Simulation	通过PASS
38.3.4.2	温度试验 Thermal test	通过PASS
38.3.4.3	振动 Vibration	通过PASS
38.3.4.4	冲击 Shock	通过PASS
38.3.4.5	外部短路 External Short Circuit	通过PASS
38.3.4.6	撞击 Impact	通过PASS
38.3.4.6	挤压 Crush	--
38.3.4.7	过度充电 Overcharge	通过PASS
38.3.4.8	强制放电 Forced discharge	通过PASS
测试实验室 Test Laboratory	东莞市安磁检测技术有限公司 Dongguan Anci Electronic Technology Co., Ltd.	
实验室地址 Laboratory Address	广东东莞市松山湖高新技术产业开发区总部2路11号A座1-2层 1-2 Floor, Building A, No.11, Headquarters 2 Road, Songshan Lake Hi-tech Industrial, Development Zone, Dongguan City, Guangdong Pr. China	
实验室电话 Laboratory Telephone	0769-85075888	
实验室网址 Laboratory Website	www.anci.com.cn	
实验室邮箱 Laboratory Email	ada@anci.com	
测试报告编号 Test Report Number	SA1911450U 02001	
测试时间 Date of performance of tests	2019-12-03 to 2019-12-17	
批准-工程经理 Approved by Engineer Manager	 系建群	发日期 Issued data 2020-01-09

Dongguan Anci Electronic Technology Co., Ltd.

Address: 1-2 Floor, Building A, No.11, Headquarters 2 Road, Songshan Lake Hi-tech Industrial, Development Zone, Dongguan City, Guangdong Pr. China

Tel: 0769-85075888 Fax: 0769-58075898

E-mail:ada@anci.com Web: www.anci.com.cn

## UN38.3 试验概要

### UN38.3 Test Summary

<b>样品信息</b> Sample Information	
样品名称 Sample Name	可充电锂离子电池组 Rechargeable Li-ion Battery
样品类型 Sample Type	锂离子电池组 Lithium ion battery
样品型号 Sample Model	GSP-1S3P-CH4A
规格参数 Specifications	3.6V 7500mAh 27Wh
锂含量 Lithium Content	--
产品质量 Product Mass	Approx 154.3g
物理描述 Physical description	方形 Prismatic 蓝黑杂色 Blue & Black
委托方 Applicant	广州鹏辉能源科技股份有限公司 Guangzhou Great Power Energy & Technology Co., Ltd.
委托方地址 Applicant Address	中国广东省广州市番禺区沙湾镇市良路（西村段）912号 NO.912, West Village Segment, Shiliang Road, Shawan Town, Panyu District, Guangzhou City, Guangdong Province 511483, P.R. China
制造商 Manufacturer	广州鹏辉能源科技股份有限公司 Guangzhou Great Power Energy & Technology Co., Ltd.
制造商地址 Manufacturer Address	中国广东省广州市番禺区沙湾镇市良路（西村段）912号 NO.912, West Village Segment, Shiliang Road, Shawan Town, Panyu District, Guangzhou City, Guangdong Province 511483, P.R. China
制造商电话 Manufacturer Telephone	020-39196888
制造商邮箱 Manufacturer Email	info@greatpower.net
制造商网址 Manufacturer Website	<a href="http://www.greatpower.net/">http://www.greatpower.net/</a>
测试标准 Test Standard	《联合国关于危险货物运输的建议书 试验和标准手册》第38.3章第六版修订1 <United Nations Recommendations on the Transport of Dangerous Goods: Manual of Tests and Criteria> (ST/SG/AC.10/11/Rev.6/Amend.1 Section 38.3)

<b>UN38.3 试验概要</b> <b>UN38.3 Test Summary</b>		
<b>Reference to assembled battery testing requirements 集成电池组试验要求:</b> <input checked="" type="checkbox"/> 不适用 Not application <input type="checkbox"/> UN38.3.3(f) <input type="checkbox"/> UN38.3.3(g)		
条款Clause	测试项目Test Item	测试结果Test Results
38.3.4.1	高度模拟 Altitude Simulation	通过PASS
38.3.4.2	温度试验 Thermal test	通过PASS
38.3.4.3	振动 Vibration	通过PASS
38.3.4.4	冲击 Shock	通过PASS
38.3.4.5	外部短路 External Short Circuit	通过PASS
38.3.4.6	撞击 Impact	通过PASS
38.3.4.6	挤压 Crush	--
38.3.4.7	过度充电 Overcharge	通过PASS
38.3.4.8	强制放电 Forced discharge	通过PASS
测试实验室 Test Laboratory	东莞市安磁检测技术有限公司 Dongguan Anci Electronic Technology Co., Ltd.	
实验室地址 Laboratory Address	广东东莞市松山湖高新技术产业开发区总部2路11号A座1-2层 1-2 Floor, Building A, No.11, Headquarters 2 Road, Songshan Lake Hi-tech Industrial, Development Zone, Dongguan City, Guangdong Pr. China	
实验室电话 Laboratory Telephone	0769-85075888	
实验室网址 Laboratory Website	www.anci.com.cn	
实验室邮箱 Laboratory Email	ada@anci.com	
测试报告编号 Test Report Number	SA1911450U 02001	
测试时间 Date of performance of tests	2019-12-03 to 2019-12-17	
批准-工程经理 Approved by Engineer Manager	 系建群	发日期 Issued data 2020-01-09