OPENS THE DOOR TO THE SMART HOME

Door Lock Drive

HmIP-DLD

No more searching for the key? The intelligent door lock drive by Homematic IP makes it possible! Unlocking, locking and opening of doors is done conveniently and securely via smartphone or remote control. The Homematic IP app keeps an eye on your entrance door at all times.





CONVENIENT & FLEXIBLE ACCESS CONTROL

It is now possible to easily lock, unlock and even open doors at any time while on the move or from the couch. Simply by Homematic IP app or key ring remote control.

Another advantage: Secure locking of the door is also possible by voice control (with Amazon Alexa or Google Assistant).

EASILY DETERMINE WHO MAY ENTER YOUR HOME

Thanks to configurable access authorisations, access to your smart home can be managed individually – no matter for which day of the week or at what time. The front door can only be opened if you want it to. This means, for example, that cleaning staff or care services can enter the house only at certain times using the key ring remote control.

IS THE FRONT DOOR REALLY LOCKED?

Thanks to time-dependent locking, this question becomes unnecessary. At a defined time, the front door is automatically locked (e.g. at night). This not only increases the security in the smart home, but also saves you from having to check the front door when it is not necessary.

If you want to be on the safe side, you can have the front door automatically locked again after each time it is unlocked. Set-points and delay times can be set individually via the app.

HIGHLY SECURE

The door lock drive benefits from the VDE-certified protocol, IT and data security of the Homematic IP system.

As it is mounted on the inside of the door, the device is not visible from the outside.

Operation requires connection to one of the following solutions:

- Homematic IP Access Point (HmIP-HAP) with free smartphone app and free cloud service
- Central Control Unit CCU2/CCU3 with the local user interface WebUI
- Third-party solutions of partners

TECHNICAL SPECIFICATIONS


Supply voltage 3x 1.5 V LR6/mignon/AA Battery life 1/2 year (typ.) Degree of protection IP20 Ambient temperature 5 to 35 °C Dimensions (W x H x D) 56 x 118 x 63 mm 328 g (including batteries) Weiaht 868.0-868.60 MHz Radio frequency band 869.4-869.65 MHz Typ. open area RF range 200 m

FASY TO RETROFIT

Easily mounted on standard profile cylinders with emergency and danger function – without damaging the door, frame or key. Thanks to battery operation, no wiring is necessary. For mounting, the lock cylinder must protrude 8-15 mm on the inside of the door.



SUITABLE FOR UNIVERSAL USE



ADDITIONAL ADVANTAGES

- ✓ Up to 8 access authorisations with individual time profiles can be created for each door lock drive
- ✓ Manual opening and closing possible at any time via the rotary wheel (emergency function)
- ✓ The door can still be opened from the outside with a standard key
- ✓ Personal PINs to protect against unauthorised operation via app

LOGISTICAL DATA

Product reference 154952A0

EAN code 4047976549528

Short description HmIP-DLD

Packing unit 30

Packing dimensions 184 x 112 x 97 mm

Weight incl. packaging 529.2 g

PACKAGE CONTENTS

Homematic IP Door Lock Drive Mounting plate Mounting material and batteries User manual