




Data Sheet

REV.1

5.5 x 2.1 mm DC 12 V 0.5A connector socket









仕様
SPECIFICATION

1. 定 格 : MJ-14SR=DC12V 0.5A
Rating : MJ-15SR=DC12V 1A
2. 絶縁抵抗 : DC500V/100MΩ以上
Insulation resistance :
DC500V/100MΩMIN.
3. 耐電圧 : AC500V 1分間。
Withstand voltage :
AC500V 1minute.
4. 接触抵抗 : 30mΩ以下
Contact resistance :
30mΩMAX
5. 本製品はRoHS対応品とする。
This product is corresponding to RoHS.



回路
CIRCUIT



	A部	適合フ'ラグ' MATE PLUG
MJ-14SR	φ2.0	φ5.5 X φ2.1
MJ-15SR	φ2.35	φ5.5 X φ2.5

7	CONTACT	CONTACTバネ	PBW	1	Ni		TOLERANCE	SCALE	DATE	DESING	DRAW	INSPE	APRO
6	NUT	六角ナット	STEEL	1	Ni		±0.3	2/1	06/7/4	K. S	N. I		M. K
5	TERMINAL	B ラグ' B	BSR t=0.3	1	Ni		MODEL	2366434	QTY	PART NAME	DC JACK DCバ' ワージ' ャック MJ-14SR, 15SR		
4	TERMINAL	A ラグ' A	BSR t=0.3	1	Ni	型式							
3	PIN	ピン	BSBM	1	Ni		MATERIAL				DRAW. NO	MJ14SR	
2	RING	リング	BSBM	1	Ni		材質				図番		
1	BODY	ボディ	PA	1			FINISH						
LET	PART NAME	MATERIAL	QTY	FINISH	NOTE	処理							